





The X-Y system features a movable 3<sup>rd</sup> track that permits precise positioning of the lifted person anywhere under the X-Y systems range.

Selection is based on distance between fasteners and the ceiling lift capacity.

The distance between fasteners is the maximum permitted between fasteners wall posts or parallel tracks of the X-Y.

*Ceiling fastened track*



# X-Y System

*KWIKtrak*

## TRACK SIZE

MAXIMUM DISTANCE BETWEEN FASTENERS FOR FIXED TRACK SECTIONS					
CEILING LIFT CAPACITY			90 MM	140 MM	180 MM
KG	LB	ST			
200	440	28.57	2.50 m	4.50 m*	6.00 m*
270	600	42.86	2.15 m	4.15 m	5.80 m
360	800	57.14	1.85 m	3.60 m	5.00 m
455	1000	71.43	1.65 m	3.20 m	4.50 m

\*Maximum length available

CEILING LIFT CAPACITY			MAXIMUM UNSUPPORTED SPAN OF THE MOVING 3 <sup>rd</sup> TRACK ON AN X-Y SYSTEM DISTANCE IS EXPRESSED IN METERS																	
KG	LB	ST	1.75	2.00	2.25	2.50	2.75	3.00	3.25	3.50	3.75	4.00	4.25	4.50	4.75	5.00	5.25	5.50	5.75	6.00
200	440	28.57	HO	HO	HO	HO	HM	HM	HM	HM	HM	HM	HM	HM	HM	HL	HL	HL	HL	HL
270	600	42.86	HO	HO	HM	HM	HM	HM	HM	HM	HM	HM	HL	HL	HL	HL	HL	HL	NR	NR
360	800	57.14	HO	HM	HM	HM	HM	HM	HM	HM	HL	HL	HL	HL	HL	HL	NR	NR	NR	NR
455	1000	71.43	HM	HM	HM	HM	HM	HM	HM	HL	HL	HL	HL	HL	NR	NR	NR	NR	NR	NR

HO - KWIKtrak 90mm - Standard span

HM - KWIKtrak 140mm - Medium span

HL - KWIKtrak 180mm - Long span

NR - Not recommended

## ACCESSORIES

A	#700.11295	XY Flush mount trolley KWIKtrak
B	#700.12300	XY Trolley Kit 455 kg KWIKtrak
C	#700.15570	XY retaining assembly KWIKtrak
D	#700.15510	XY Charger Interface KWIKtrak (To use with #700.11290)
E	#700.11285	XY Short trolley

